

ST-EMS60



Embedded Railroad Pole, 60 ft

- Quick deploy embedment
- Rivet nut mounting

Product Classification

Product Type Monopole

Dimensions

Height 18.3 m | 60.0 ft
Mounting Diameter, maximum 482.6 mm | 19 in
Mounting Diameter, minimum 254.0 mm | 10 in

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Embedded
Monopole Capability Type Heavy duty
Application Positive train control/Centralized traffic control (PTC/CTC communications)
Equipment Load Rating 4 ft microwave reflector | Omni antenna | Telecommunications unit
Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs
Material Type Hot dip galvanized steel
Monopole Design Multi-sided
Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts
Package Quantity 1