

ST-DBH60



Double Hinged Pole, 60 ft

- Hoist-operated, counterbalanced hinged design
- No climbing necessary for equipment installation
- Single person service
- Rivet nut mounting
- Secure locking

Product Classification

Product Type Monopole

Dimensions

Height 18.3 m | 60.0 ft
Mounting Diameter, maximum 342.9 mm | 13 1/2 in
Mounting Diameter, minimum 199.6 mm | 7.9 in
Weight 910.8 kg | 2008.0 lb

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Base
Monopole Capability Type Heavy duty
Application Positive train control/Centralized traffic control (PTC/CTC communications)
Equipment Load Rating 2 ft microwave reflector | Solar panel | Telecommunications unit
Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs
Material Type Hot dip galvanized steel
Monopole Design Round conical
Optional Accessories Antenna mounts | Cabinet mounts | Hoist | Solar mounts
Package Quantity 1