



Self-locking Hanger with Non transverse tab for 1-5/8 in RADIAX® Radiating cable

## Product Classification

**Product Type** Hanger kit

## Dimensions

<b>Nominal Size</b>	1-5/8 in
<b>Compatible Diameter, maximum</b>	50.500 mm   1.988 in
<b>Compatible Diameter, minimum</b>	46.500 mm   1.831 in
<b>Height</b>	72.80 mm   2.87 in
<b>Length</b>	53.50 mm   2.11 in
<b>Width</b>	22.00 mm   0.87 in

## Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

## General Specifications

<b>Hanger Type</b>	Self locking hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Material Type</b>	Polyamide PA12
<b>Maximum Stack Height</b>	2
<b>Package Quantity</b>	25

## Mechanical Specifications

<b>Flammability Test Method</b>	UL 94-HB
<b>Maximum Load</b>	1400 N   315 lbf
<b>Toxicity Index Test Method</b>	IEC 60754-2
<b>UV Resistance, minimum with no degradation</b>	=500 hours exposure in accelerated UV life chamber

## Packed Dimensions

<b>Height</b>	11.5 cm   4.5 in
<b>Length</b>	30.0 cm   11.8 in
<b>Shipping Weight</b>	2.10 kg   4.63 lb
<b>Width</b>	8.5 cm   3.3 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power