



HELIAX® FiberFeed® Hanger Kit, 4 holes x 6.0 mm (FJ-2SM-series cables) and 4 holes x 10.1 mm (PWRT-212-S cables) grommet, 1 x SSH-158 Snap-in hanger (designed to organize multiple cables, not intended to support the weight of the cable for long vertical runs up a tower)

Product Classification

Brand FiberFeed® | HELIAX®
Product Type Hanger kit

Dimensions

Nominal Size 1-5/8 in
Height 56.00 mm | 2.20 in
Width 55.00 mm | 2.17 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Hanger kits
Cables per Hanger 8
Color Black | Silver
Material Type Stainless steel
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation =500 hours in salt spray chamber
Mounting 3/8 in (M10) drilled cable ladder
Vibration Survival =4 hours at resonant frequency

Packed Dimensions

Height 26.0 cm | 10.2 in

Length	9.0 cm 3.5 in
Shipping Weight	0.53 kg 1.16 lb
Width	9.0 cm 3.5 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products

SSH-158 — SnapStak® Hanger for 1-5/8 in coaxial cable

SSH-XL — SnapStak® Plus Adjustable Hanger for 36mm to 51mm Cable - No Grommets Required. For patents, see www.cs-pat.com.