



HELIAX® FiberFeed® Hanger Kit, 4 holes x 6.0 mm (FJ-2SM-series cables) and 4 holes x 12.4 mm (PWRT-210-S cables) grommet, 1 x SSH-158 Snap-in hanger (designed to organize multiple cables, not intended to support the weight of the cable for long vertical runs up a tower)

## Product Classification

**Brand** FiberFeed® | HELIAX®  
**Product Type** Hanger kit

## Dimensions

**Nominal Size** 1-5/8 in  
**Height** 56.00 mm | 2.20 in  
**Width** 55.00 mm | 2.17 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

**Hanger Type** Hanger kits  
**Cables per Hanger** 8  
**Color** Black | Silver  
**Material Type** Stainless steel  
**Package Quantity** 10

## Mechanical Specifications

**Corrosion Resistance, minimum with no degradation** =500 hours in salt spray chamber  
**Mounting** 3/8 in (M10) drilled cable ladder  
**Vibration Survival** =4 hours at resonant frequency

## Packed Dimensions

**Height** 26.0 cm | 10.2 in

<b>Length</b>	9.0 cm   3.5 in
<b>Shipping Weight</b>	0.53 kg   1.16 lb
<b>Width</b>	9.0 cm   3.5 in

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

