



HELIAX® FiberFeed® Hanger Kit, 3 holes x 6.0 mm (FJ-2SM-series cables) and 3 holes x 14.2 mm (PWRT-208-S cables) grommet, 1 x SSH-158 Snap-in hanger (designed to organize multiple cables, not intended to support the weight of the cable for long vertical runs up a tower)

**OBSOLETE**

## Product Classification

<b>Brand</b>	HELIAX®
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	1-5/8 in
<b>Height</b>	56.00 mm   2.20 in
<b>Width</b>	55.00 mm   2.17 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Hanger kits
<b>Cables per Hanger</b>	6
<b>Color</b>	Black   Silver
<b>Material Type</b>	Stainless steel
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	=500 hours in salt spray chamber
<b>Mounting</b>	3/8 in (M10) drilled cable ladder
<b>Vibration Survival</b>	=4 hours at resonant frequency

## Packed Dimensions

<b>Height</b>	26.0 cm   10.2 in
<b>Length</b>	9.0 cm   3.5 in
<b>Shipping Weight</b>	0.53 kg   1.16 lb
<b>Width</b>	9.0 cm   3.5 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

