



Cushion Insert with 1 hole for HELIAX® FiberFeed® cables (Fusion tape included)

Product Classification

Brand	I-Line
Product Type	Cushion insert

Dimensions

Nominal Size	1-1/4 in
Height	82.55 mm 3.25 in
Length	25.40 mm 1.00 in

General Specifications

Cable Type	Hybrid fiber
Cables per Cushion	1
Color	Black
Includes	Cushion
Material Type	EPDM rubber
Ordering Note	CommScope® non-standard product
Package Quantity	1

Mechanical Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packed Dimensions

Height	169.9 mm 6.7 in
Length	99.8 mm 3.9 in
Shipping Weight	0.50 kg 1.10 lb
Width	129.8 mm 5.1 in

Included Products

294701-T

FT-TB — Black Self-fusing Tape, 15 ft

Black Self-fusing Tape, 15 ft



Product Classification

Product Type Weatherproofing tape

Dimensions

Length 4.57 m | 15.00 ft
Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in
Width 38.10 mm | 1.50 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit Four 1/2 in–1/2 in | One 1/2 in–2-1/4 in | Two 1/2 in–7/8 in | Two 1/2 in–7/8 in to device
Color Black
Material Type Silicone tape
Ordering Note CommScope® non-standard product
Package Quantity 2

Mechanical Specifications

UV Resistance Test Method ASTM D518, Test Method B
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 8.3 cm | 3.3 in
Length 0.6 cm | 0.3 in
Shipping Weight 0.10 kg | 0.21 lb
Width 8.3 cm | 3.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

