

# 19256B-C



Lace-up Hoisting Grip with tie wraps for HELIAX® FiberFeed® cables

## Product Classification

**Product Type** Hoisting grip

## Dimensions

**Nominal Size** 7/8 in  
**Grip Length, minimum** 431.80 mm | 17.00 in  
**Leader Length, minimum** 330.20 mm | 13.00 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## General Specifications

**Hoisting Grip Type** Lace-up hoisting grip  
**Attachment Spacing Intervals** 61 m | 200 ft  
**Material Type** Stainless steel  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 1  
**Support Clamp** Not included  
**Tool Type** Hoisting grip

## Mechanical Specifications

**Pull Load Capacity** 500 lb

## Packed Dimensions

**Height** 3.8 cm | 1.5 in  
**Length** 22.2 cm | 8.7 in  
**Width** 21.8 cm | 8.6 in  
**Shipping Weight** 0.22 kg | 0.49 lb

## Regulatory Compliance/Certifications

| Agency                     | Classification   |
|----------------------------|--|
| RoHS 2011/65/EU            | Compliant  |
| ISO 9001:2015              | Designed, manufactured and/or distributed under this quality management system |
| China RoHS SJ/T 11364-2014 | Above Maximum Concentration Value (MCV)  |

