

BLK-RIFC-A04B0

Fiber Optic Ribbon Breakout Kit, 12F/ribbon, 72F/tube, 5-8 mm central tube outside diameter, 4 tubes/leg

Product Classification

Product Series	BLK-R
Product Type	Fiber breakout kit, rectangular
Regional Availability	Latin America North America

Dimensions

Central Tube Outer Diameter	5 mm – 8 mm (0.20 in – 0.33 in)
Tube Length	5.0 m 16.4 ft

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Application	For use with ribbon fiber cables
Breakout Legs, quantity	1
Fibers per Ribbon, maximum	12
Fibers per Tube, maximum	72
Package Quantity	1
Packaging Type	Bag Carton
Tube Type	Ribbon IFC
Tubes per Leg, quantity	4

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

