

# BLK-RCT-B12E0

---

Fiber Optic Ribbon Breakout Kit, 24/36F/ribbon, 576/720/864F/tube (12/leg), 15-20 mm central tube out. dia.

## Product Classification

<b>Product Series</b>	BLK-R
<b>Product Type</b>	Fiber breakout kit, rectangular
<b>Regional Availability</b>	Latin America   North America

## Dimensions

<b>Central Tube Outer Diameter</b>	15 mm – 20 mm (0.60 in – 0.80 in )
<b>Tube Length</b>	5.0 m   16.4 ft

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
----------------------------	---------

## General Specifications

<b>Application</b>	For use with ribbon fiber cables
<b>Breakout Legs, quantity</b>	1
<b>Fibers per Ribbon, maximum</b>	60
<b>Fibers per Tube, maximum</b>	2160
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Tube Type</b>	Ribbon central tube
<b>Tubes per Leg, quantity</b>	12

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

