

BLK-RCT-B09E0

Fiber Optic Ribbon Breakout Kit, 24F/ribbon, 576/720/864F/tube, 15-20 mm central tube outside dia., 9 tubes/leg

Product Classification

Product Series	BLK-R
Product Type	Fiber breakout kit, rectangular
Regional Availability	Latin America North America

Dimensions

Central Tube Outer Diameter	15 mm – 20 mm (0.60 in – 0.80 in)
Tube Length	5.0 m 16.4 ft

Environmental Specifications

Environmental Space	Outdoor
----------------------------	---------

General Specifications

Application	For use with ribbon fiber cables
Breakout Legs, quantity	1
Fibers per Ribbon, maximum	24
Fibers per Tube, maximum	2160
Package Quantity	1
Packaging Type	Bag Carton
Tube Type	Ribbon central tube
Tubes per Leg, quantity	9

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

