

BLK-RIFC-A03CO

Fiber Optic Ribbon Breakout Kit, 12F/ribbon, 108-216F/tube, 8-11 mm central tube outside dia., 2 tubes/leg

Product Classification

Product Series	BLK-R
Product Type	Fiber breakout kit, rectangular
Regional Availability	Latin America North America

Dimensions

Central Tube Outer Diameter	8 mm – 11 mm (0.33 in – 0.43 in)
Tube Length	5.0 m 16.4 ft

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Application	For use with ribbon fiber cables
Breakout Legs, quantity	1
Fibers per Ribbon, maximum	12
Fibers per Tube, maximum	324
Package Quantity	1
Packaging Type	Bag Carton
Tube Type	Ribbon IFC
Tubes per Leg, quantity	3

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

