

# BLK-RCT-A03B0

---

Fiber Optic Ribbon Breakout Kit, 1-12F/ribbon, 12-96F/tube, 5-8 mm central tube outside dia., 3 tubes/leg

## Product Classification

<b>Product Series</b>	BLK-R
<b>Product Type</b>	Fiber breakout kit, rectangular
<b>Regional Availability</b>	Latin America   North America

## Dimensions

<b>Central Tube Outer Diameter</b>	5 mm – 8 mm (0.20 in – 0.33 in )
<b>Tube Length</b>	5.0 m   16.4 ft

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
----------------------------	---------

## General Specifications

<b>Application</b>	For use with ribbon fiber cables
<b>Breakout Legs, quantity</b>	1
<b>Fibers per Ribbon, maximum</b>	12
<b>Fibers per Tube, maximum</b>	108
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Tube Type</b>	Ribbon central tube
<b>Tubes per Leg, quantity</b>	3

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

