

# BLK-RLBT-A01060

---

Fiber Optic Ribbon Breakout Kit, 12F/ribbon, 72F/tube, 1 tube/leg

## Product Classification

|                              |                                 |
|------------------------------|---------------------------------|
| <b>Product Series</b>        | BLK-R                           |
| <b>Product Type</b>          | Fiber breakout kit, rectangular |
| <b>Regional Availability</b> | Latin America   North America   |

## Dimensions

|                    |                 |
|--------------------|-----------------|
| <b>Tube Length</b> | 5.0 m   16.4 ft |
|--------------------|-----------------|

## Environmental Specifications

|                            |         |
|----------------------------|---------|
| <b>Environmental Space</b> | Outdoor |
|----------------------------|---------|

## General Specifications

|                                   |                                  |
|-----------------------------------|----------------------------------|
| <b>Application</b>                | For use with ribbon fiber cables |
| <b>Breakout Legs, quantity</b>    | 6                                |
| <b>Fibers per Ribbon, maximum</b> | 12                               |
| <b>Fibers per Tube, maximum</b>   | 72                               |
| <b>Package Quantity</b>           | 1                                |
| <b>Packaging Type</b>             | Bag   Carton                     |
| <b>Tube Type</b>                  | Ribbon in loose buffer tube      |
| <b>Tubes per Leg, quantity</b>    | 1                                |

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

