

# DHK-158-2-P



Double Hanger Kit for 1-5/8 in coaxial cable, single stack; includes hardware and angle adapter

## Product Classification

<b>Brand</b>	ValuSite™
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	1-5/8 in
<b>Compatible Diameter, maximum</b>	50.800 mm   2.000 in
<b>Compatible Diameter, minimum</b>	49.022 mm   1.930 in
<b>Height</b>	78.92 mm   3.11 in
<b>Length</b>	144.60 mm   5.69 in
<b>Width</b>	25.92 mm   1.02 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Composite clamp
<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Includes</b>	Angle adapter   Hardware
<b>Material Type</b>	Engineered plastic   Stainless steel
<b>Maximum Stack Height</b>	1
<b>Ordering Note</b>	CommScope® standard product in Mexico, Central America, and South America
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	M8 hardware
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	38.1 cm   15.0 in
<b>Length</b>	7.6 cm   3.0 in
<b>Shipping Weight</b>	0.57 kg   1.25 lb
<b>Width</b>	38.1 cm   15.0 in

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power