

# DHK-158-4-P



Double Hanger Kit for 1-5/8 in coaxial cable, double stack; includes hardware and angle adapter

## **OBSOLETE**

This product was discontinued on: June 30, 2013

### Replaced By

DHK-158-6-P

Double Hanger Kit for 1-5/8 in coaxial cable, triple stack; includes hardware and angle adapter

## Product Classification

Brand	ValuSite™
Product Type	Hanger kit

## Dimensions

Nominal Size	1-5/8 in
Compatible Diameter, maximum	50.800 mm   2.000 in
Compatible Diameter, minimum	49.022 mm   1.930 in
Height	157.84 mm   6.21 in
Length	144.60 mm   5.69 in
Width	25.92 mm   1.02 in

## Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

## Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
-----------------------	--------------------------------------

## General Specifications

Hanger Type	Composite clamp
Cables per Hanger	4
Color	Black
Includes	Angle adapter   Hardware

# DHK-158-4-P

---

<b>Material Type</b>	Engineered plastic   Stainless steel
<b>Maximum Stack Height</b>	2
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	M8 hardware
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	38.1 cm   15.0 in
<b>Length</b>	7.6 cm   3.0 in
<b>Shipping Weight</b>	0.68 kg   1.50 lb
<b>Width</b>	38.1 cm   15.0 in

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power