

BHD-78



Double Block Hanger for 7/8 in coaxial cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 7/8 in
Compatible Diameter, maximum 28.194 mm | 1.110 in
Compatible Diameter, minimum 27.686 mm | 1.090 in
Height 43.00 mm | 1.69 in
Length 80.00 mm | 3.15 in
Width 40.00 mm | 1.57 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Double block hanger
Cables per Hanger 2
Color Black
Material Type 30% glass filled polypropylene (PP)
Maximum Stack Height 3
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Mounting 3/8 in (M10) drilled cable ladder
UV Resistance, minimum with no degradation =100 hours exposure in accelerated UV life chamber
Environmental Strength Capability Double cable weight

BHD-78

Packed Dimensions

Height	5.1 cm 2.0 in
Length	22.9 cm 9.0 in
Shipping Weight	0.56 kg 1.23 lb
Width	17.8 cm 7.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power