



Double Block Hanger for 1-1/4 in coaxial cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-1/4 in
Compatible Diameter, maximum 40.640 mm | 1.600 in
Compatible Diameter, minimum 39.624 mm | 1.560 in
Height 49.00 mm | 1.93 in
Length 110.00 mm | 4.33 in
Width 56.00 mm | 2.20 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Double block hanger
Cables per Hanger 2
Color Black
Material Type 30% glass filled polypropylene (PP)
Maximum Stack Height 3
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Mounting 3/8 in (M10) drilled cable ladder
UV Resistance, minimum with no degradation =100 hours exposure in accelerated UV life chamber
Environmental Strength Capability Double cable weight

BHD-114

Packed Dimensions

Height	5.1 cm 2.0 in
Length	30.5 cm 12.0 in
Shipping Weight	0.99 kg 2.17 lb
Width	20.3 cm 8.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power