

BHD-158



Double Block Hanger for 1-5/8 in coaxial cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-5/8 in
Compatible Diameter, maximum 51.054 mm | 2.010 in
Compatible Diameter, minimum 49.530 mm | 1.950 in
Height 48.00 mm | 1.89 in
Length 137.00 mm | 5.39 in
Width 71.00 mm | 2.80 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Double block hanger
Cables per Hanger 2
Color Black
Material Type 30% glass filled polypropylene (PP)
Maximum Stack Height 3
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Mounting 3/8 in (M10) drilled cable ladder
UV Resistance, minimum with no degradation =100 hours exposure in accelerated UV life chamber
Environmental Strength Capability Double cable weight

BHD-158

Packed Dimensions

Height	5.1 cm 2.0 in
Length	30.5 cm 12.0 in
Shipping Weight	1.38 kg 3.04 lb
Width	25.4 cm 10.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power