



Single Block Hanger for 1-1/4 in coaxial cable

## Product Classification

**Product Type** Hanger kit

## Dimensions

**Nominal Size** 1-1/4 in  
**Compatible Diameter, maximum** 40.640 mm | 1.600 in  
**Compatible Diameter, minimum** 39.624 mm | 1.560 in  
**Height** 51.00 mm | 2.01 in  
**Length** 67.00 mm | 2.64 in  
**Width** 60.00 mm | 2.36 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

**Hanger Type** Single block hanger  
**Cables per Hanger** 1  
**Color** Black  
**Material Type** 30% glass filled polypropylene (PP)  
**Maximum Stack Height** 3  
**Ordering Note** CommScope® standard product in the United States and Canada  
**Package Quantity** 10

## Mechanical Specifications

**Mounting** 3/8 in (M10) drilled cable ladder  
**UV Resistance, minimum with no degradation** =100 hours exposure in accelerated UV life chamber  
**Environmental Strength Capability** Double cable weight

## Packed Dimensions

<b>Height</b>	5.1 cm   2.0 in
<b>Length</b>	25.4 cm   10.0 in
<b>Shipping Weight</b>	0.86 kg   1.90 lb
<b>Width</b>	17.8 cm   7.0 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power