



Single Block Hanger for 1-5/8 in coaxial cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-5/8 in
Compatible Diameter, maximum 51.054 mm | 2.010 in
Compatible Diameter, minimum 49.530 mm | 1.950 in
Height 51.00 mm | 2.01 in
Length 81.00 mm | 3.19 in
Width 71.00 mm | 2.80 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Single block hanger
Cables per Hanger 1
Color Black
Material Type 30% glass filled polypropylene (PP)
Maximum Stack Height 3
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Mounting 3/8 in (M10) drilled cable ladder
UV Resistance, minimum with no degradation =100 hours exposure in accelerated UV life chamber
Environmental Strength Capability Double cable weight

Packed Dimensions

Height	5.1 cm 2.0 in
Length	25.4 cm 10.0 in
Shipping Weight	1.02 kg 2.25 lb
Width	25.4 cm 10.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power