



TDUX - Inflatable Duct Seal, size 90

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentally friendly, non-toxic and resistant to chemicals

Product Classification

Product Type	Cable duct seal
Product Series	TDUX
Regional Availability	Latin America North America

Dimensions

Cable Diameter, maximum	83.00 mm
Cable Diameter, minimum	22.00 mm
Conduit Inner Diameter, maximum	100.00 mm
Conduit Inner Diameter, minimum	60.00 mm
Length	422.00 mm
Width	120.00 mm

Environmental Specifications

Installation Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
---------------------------------	-------------------------------------

General Specifications

Includes	Inflatable bladder with sealing mechanism
Ordering Note	When sealing more than two cables in a duct, separate orderable TDUX-CL clips are to be used
Package Quantity	10

Outline Drawing

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

