



## TDUX - Inflatable Duct Seal, size 60

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentally friendly, non-toxic and resistant to chemicals

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Product Type</b>          | Cable duct seal               |
| <b>Product Series</b>        | TDUX                          |
| <b>Regional Availability</b> | Latin America   North America |

## Dimensions

|  |           |
|--|-----------|
| <b>Cable Diameter, maximum</b>         | 45.00 mm  |
| <b>Cable Diameter, minimum</b>         | 18.00 mm  |
| <b>Conduit Inner Diameter, maximum</b> | 60.00 mm  |
| <b>Conduit Inner Diameter, minimum</b> | 45.00 mm  |
| <b>Length</b>                          | 262.00 mm |
| <b>Width</b>                           | 120.00 mm |

## Environmental Specifications

|                                 |                                     |
|---------------------------------|-------------------------------------|
| <b>Installation Temperature</b> | -5 °C to +40 °C (+23 °F to +104 °F) |
|---------------------------------|-------------------------------------|

## General Specifications

|                         |  |
|-------------------------|--|
| <b>Includes</b>         | Inflatable bladder with sealing mechanism  |
| <b>Ordering Note</b>    | When sealing more than two cables in a duct, separate orderable TDUX-CL clips are to be used |
| <b>Package Quantity</b> | 10   |

## Outline Drawing

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

