



TDUX - Inflatable Duct Seal, size 90

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentally friendly, non-toxic and resistant to chemicals

Product Classification

Product Type	Cable duct seal
Product Series	TDUX
Regional Availability	EMEA

Dimensions

Cable Diameter, maximum	90.00 mm
Cable Diameter, minimum	45.00 mm
Conduit Inner Diameter, maximum	110.00 mm
Conduit Inner Diameter, minimum	75.00 mm
Length	482.00 mm
Width	120.00 mm

Environmental Specifications

Installation Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
---------------------------------	-------------------------------------

General Specifications

Includes	Inflatable bladder with sealing mechanism
Ordering Note	When sealing more than two cables in a duct, separate orderable TDUX-CL clips are to be used
Package Quantity	10

Outline Drawing

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

