

HSG-M29-ADPT-L



HELIAX® SureGuard® sealing adapter for fully threaded device ports that will form a weather seal with the HELIAX® SureGuard Boots (HSG-LDF4, HSG-LDF4-DR, HSG-FSJ4 and HSG-FSJ4-DR)

Product Classification

Brand	HELIAX® SureGuard®
Product Type	Weatherproofing boot

Dimensions

Inner Diameter	28.30 mm 1.11 in
Length	14.60 mm 0.57 in
Width	41.00 mm 1.61 in

Environmental Specifications

Installation Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)

General Specifications

Application	Provides moisture seal for fully threaded device ports
Applications per Kit	Ten device connections
Color	Black
Material Type	Thermoplastic elastomer (TPE)
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Device Port Interface	7-16 DIN Female
Thread Size	M29
UV Resistance Test Method	ASTM G154-12a
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	IEC 60068-2-11 IEC 60529:2001, IP68

HSG-M29-ADPT-L

Packed Dimensions

Height	15.0 mm 0.6 in
Length	140.0 mm 5.5 in
Shipping Weight	55.00 g 0.12 lb
Width	120.0 mm 4.7 in