



SnapTak PIM-guard Adjustable Hanger for 10.1 mm to 14.0 mm Cable – PIM Free Polymer Construction. No Grommets Required.

Product Classification

Brand	SnapTak PIM-guard
Product Type	Hanger kit

Dimensions

Compatible Diameter, maximum	14.000 mm 0.551 in
Compatible Diameter, minimum	10.100 mm 0.398 in
Height	27.20 mm 1.07 in
Length	32.00 mm 1.26 in
Width	32.00 mm 1.26 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Accessories	Hangers
Cables per Hanger	1
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Maximum Stack Height, Coaxial	3
Ordering Note	CommScope® standard product in Asia Pacific CommScope® standard product in Mexico, Central America, and South America CommScope® standard product in the United States and Canada

Package Quantity 10

Mechanical Specifications

Mounting 3/4 in drilled cable ladder
UV Resistance, minimum with no degradation =1000 hours exposure in accelerated UV life chamber
Vibration Survival =4 hours at resonant frequency
Environmental Strength Capability Double cable weight

Packed Dimensions

Height 30.5 mm | 1.2 in
Length 254.0 mm | 10.0 in
Shipping Weight 0.54 kg | 1.19 lb
Width 203.2 mm | 8.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power