



Furcation Tubing for Optical Fiber, indoor, no jacket, TPE tubing, 0.44/0.92 mm, orange

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

## Product Classification

### Product Type

Furcation tubing

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

## Dimensions

### Inner Diameter, nominal

0.440 mm | 0.017 in

### Length

14400.00 ft

### Outer Diameter, nominal

0.920 mm | 0.036 in

### Weight

0.6 kg/km

## Environmental Specifications

### Environmental Space

Indoor

### Installation Temperature

-0 °C to +70 °C (-32 °F to +158 °F)

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

### Application

For use with all fiber connector types | For use with singlemode and multimode optical fibers

### Color

Orange

### Package Quantity

1

### Packaging Type

Reel

## Material Specifications

### Material Type

Elastomer | Thermoplastic polyester


## Mechanical Specifications

**Minimum Bend Radius, Installation** 3.00 mm

**Minimum Bend Radius, Long Term** 5.00 mm

**Shrinkage, maximum** 0 ppm

## Outline Drawing



## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

