



Furcation Tubing for Optical Fiber, indoor, no jacket, TPE tubing, 0.44/0.92 mm, green

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

Product Classification

Product Type

Furcation tubing

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Dimensions

Inner Diameter, nominal

0.440 mm | 0.017 in

Length

14400.00 ft

Outer Diameter, nominal

0.920 mm | 0.036 in

Weight

0.6 kg/km

Environmental Specifications

Environmental Space

Indoor

Installation Temperature

-0 °C to +70 °C (-32 °F to +158 °F)

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Application

For use with all fiber connector types | For use with singlemode and multimode optical fibers

Color

Green

Package Quantity

1

Packaging Type

Reel

Material Specifications

Material Type

Elastomer | Thermoplastic polyester


Mechanical Specifications

Minimum Bend Radius, Installation 3.00 mm

Minimum Bend Radius, Long Term 5.00 mm

Shrinkage, maximum 0 ppm

Outline Drawing



Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

