



Furcation Tubing for Optical Fiber, indoor, no jacket, TPE tubing, 0.44/0.92 mm,yellow

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

Product Classification

Product Type	Furcation tubing
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Inner Diameter, nominal	0.440 mm 0.017 in
Length	14400.00 ft
Outer Diameter, nominal	0.920 mm 0.036 in
Weight	0.6 kg/km

Environmental Specifications

Environmental Space	Indoor
Installation Temperature	-0 °C to +70 °C (-32 °F to +158 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Application	For use with all fiber connector types For use with singlemode and multimode optical fibers
Color	Yellow
Package Quantity	1
Packaging Type	Reel


Material Specifications

Material Type	Elastomer Thermoplastic polyester
----------------------	-------------------------------------

Mechanical Specifications

Minimum Bend Radius, Installation	3.00 mm
Minimum Bend Radius, Long Term	5.00 mm
Shrinkage, maximum	0 ppm

Outline Drawing



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

