

Furcation Tubing for Optical Fiber, indoor, polyurethane jacket, TPE tubing, 0.44/2.0 mm, with strength member, yellow

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

Product Classification

Product Type	Furcation tubing
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Inner Diameter, nominal	0.440 mm 0.017 in
Length	1000.00 m
Outer Diameter, nominal	2.000 mm 0.079 in
Weight	2.8 kg/km

Environmental Specifications

Environmental Space	Indoor
Installation Temperature	-0 °C to +60 °C (-32 °F to +140 °F)
Operating Temperature	-0 °C to +60 °C (+32 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Application	For use with all fiber connector types For use with singlemode and multimode optical fibers
Color	Yellow
Includes	Aramid strength members
Package Quantity	1
Packaging Type	Reel


Material Specifications

Material Type	Elastomer Polyurethane Thermoplastic polyester
----------------------	--

Mechanical Specifications

Minimum Bend Radius, Installation	3.00 mm
Minimum Bend Radius, Long Term	5.00 mm
Shrinkage, maximum	0 ppm

Outline Drawing



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

