



FAST Weatherproofing Gel Sealed Grounding Transition Boot, ground line on 7/8 inch Feeder

- Gel-sealed weatherproofing boots for sealing coaxial cable connection points providing an efficient moisture block
- Wraparound design eliminates the need to disconnect the connectors before installation
- No tape, no mastics or tools required for installation and removal

Product Classification

Product Series	FAST
Product Type	Weatherproofing boot
Regional Availability	Asia

Dimensions

Cable Diameter for Seal, maximum	29.00 mm 1.14 in
Cable Diameter for Seal, minimum	27.00 mm 1.06 in
Inner Diameter	32.00 mm 1.26 in
Length	55.00 mm 2.17 in

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Weatherproofing Method	IP68

General Specifications

Application	Ground line on 7/8" Feeder
Color	Black
Material Type	Engineered plastic
Package Quantity	1

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

