



GSIC Weatherproofing Gel Sealed In-line Transition Boot, 1/2 inch to 1 5/8 inch cable

- Gel-sealed weatherproofing boots for sealing coaxial cable connection points providing an efficient moisture block
- Wraparound design eliminates the need to disconnect the connectors before installation
- No tape, no mastics or tools required for installation and removal

Product Classification

| | |
|------------------------------|----------------------|
| Product Series | GSIC |
| Product Type | Weatherproofing boot |
| Regional Availability | Asia EMEA |

Dimensions

| | |
|---|---------------------|
| Cable Diameter for Seal, maximum | 17.00 mm 52.00 mm |
| Cable Diameter for Seal, minimum | 13.00 mm 49.50 mm |
| Inner Diameter | 68.00 mm 2.68 in |
| Length | 208.00 mm 8.19 in |

Environmental Specifications

| | |
|-------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Weatherproofing Method | IP68 |

General Specifications

| | |
|-------------------------|------------------------------|
| Application | 1/2" Jumper to 1 5/8" Feeder |
| Color | Black |
| Material Type | Engineered plastic |
| Package Quantity | 1 |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

