



GSIC Weatherproofing Gel Sealed In-line Transition Boot, 1/2 inch to 7/8 inch cable

- Gel-sealed weatherproofing boots for sealing coaxial cable connection points providing an efficient moisture block
- Wraparound design eliminates the need to disconnect the connectors before installation
- No tape, no mastics or tools required for installation and removal

Product Classification

Product Series	GSIC
Product Type	Weatherproofing boot
Regional Availability	EMEA

Dimensions

Cable Diameter for Seal, maximum	17.00 mm 29.00 mm
Cable Diameter for Seal, minimum	13.00 mm 27.00 mm
Inner Diameter	43.00 mm 1.69 in
Length	147.00 mm 5.79 in

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Weatherproofing Method	IP68

General Specifications

Application	1/2" Jumper to 7/8" Feeder
Color	Black
Material Type	Engineered plastic
Package Quantity	1

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

