



Jackmoon Triplex Duct Plug, Size 4.10, for up to 3 cables with outer diameter between 32.0 and 36.1 mm

- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage
- Split design for retrofitting without disassembly

## Product Classification

<b>Brand</b>	Jackmoon®
<b>Product Type</b>	Duct plug, triplex
<b>Regional Availability</b>	EMEA   Latin America   North America

## Dimensions

<b>Cable Diameter, maximum</b>	36.10 mm
<b>Cable Diameter, minimum</b>	32.00 mm
<b>Conduit Inner Diameter, maximum</b>	109.00 mm
<b>Conduit Inner Diameter, minimum</b>	105.70 mm

## Environmental Specifications

<b>Environmental Space</b>	Handholes   Manholes
<b>Qualification Standards</b>	IEC 60068-2-17, 5 m waterhead

## General Specifications

<b>Application</b>	Cables   Pipes   Subducts
<b>Body Style</b>	Round
<b>Cables/Pipes Supported, quantity</b>	3
<b>Color</b>	White
<b>Package Quantity</b>	1

## Material Specifications

<b>Material Type</b>	PVC
<b>Sealant Type</b>	Chloroprene rubber

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

