



Jackmoon Triplex Duct Plug, Size 5.80, for up to 3 cables with outer diameter between 30.0 and 34.5 mm

- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage
- Split design for retrofitting without disassembly

Product Classification

Brand	Jackmoon®
Product Type	Duct plug, triplex
Regional Availability	EMEA Latin America North America

Dimensions

Cable Diameter, maximum	34.50 mm
Cable Diameter, minimum	30.00 mm
Conduit Inner Diameter, maximum	151.90 mm
Conduit Inner Diameter, minimum	147.80 mm

Environmental Specifications

Environmental Space	Handholes Manholes
Qualification Standards	IEC 60068-2-17, 5 m waterhead

General Specifications

Application	Cables Pipes Subducts
Body Style	Round
Cables/Pipes Supported, quantity	3
Color	Green
Package Quantity	1

Material Specifications

Material Type	PVC
Sealant Type	Chloroprene rubber

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU	Classification	Compliant
---------------	-----------------	-----------------------	-----------

