



Jackmoon Triplex Duct Plug, Size 5.80, for up to 3 cables with outer diameter between 33.0 and 36.1 mm

- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage
- Split design for retrofitting without disassembly

Product Classification

| | |
|------------------------------|--------------------------------------|
| Brand | Jackmoon® |
| Product Type | Duct plug, triplex |
| Regional Availability | EMEA Latin America North America |

Dimensions

| | |
|--|-----------|
| Cable Diameter, maximum | 36.10 mm |
| Cable Diameter, minimum | 33.00 mm |
| Conduit Inner Diameter, maximum | 151.90 mm |
| Conduit Inner Diameter, minimum | 147.80 mm |

Environmental Specifications

| | |
|--------------------------------|-------------------------------|
| Environmental Space | Handholes Manholes |
| Qualification Standards | IEC 60068-2-17, 5 m waterhead |

General Specifications

| | |
|---|---------------------------|
| Application | Cables Pipes Subducts |
| Body Style | Round |
| Cables/Pipes Supported, quantity | 3 |
| Color | Green |
| Package Quantity | 1 |

Material Specifications

| | |
|----------------------|--------------------|
| Material Type | PVC |
| Sealant Type | Chloroprene rubber |

Regulatory Compliance/Certifications

| | | | |
|---------------|-----------------|-----------------------|-----------|
| Agency | RoHS 2011/65/EU | Classification | Compliant |
|---------------|-----------------|-----------------------|-----------|

