



TENIO™ Splice Tray for large closures (C6 size) for up to 24 heat shrink splice protectors (SMOUV 45 mm)

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays
- Loop-back facility allowing for single circuit uncut looped fiber storage on the splice tray
- Compliant with most splice types and independent of any optical fiber construction

Product Classification

Product Type	Fiber splice tray
Product Series	TENIO
Regional Availability	EMEA Latin America

General Specifications

Color	Gray
Package, quantity	12
Packaging Type	Bag Carton
Splice Protector Diameter, maximum	5.00 mm 0.20 in
Splice Protector Diameter, minimum	3.50 mm 0.14 in
Splice Protector Length, maximum	45.00 mm 1.77 in
Splice Protector Length, minimum	35.00 mm 1.38 in
Splice Tray Chip Type	Heat shrink
Splice Tray Included, quantity	1
Splices per Tray, quantity	24

Dimensions

Weight	0.10 kg 0.22 lb
---------------	-------------------

Mechanical Specifications

Material Type	PBT PET
Minimum Bend Radius, standard	30.00 mm 1.18 in

Environmental Specifications

Environmental Space	Outdoor
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

