

CT-460-100



Cable Tie, Heat Stabilized, Weather-resistant, 460 mm length, 100 pcs

Product Classification

Product Type Cable tie

Dimensions

Compatible Diameter, maximum 127.000 mm | 5.000 in

Compatible Diameter, minimum 4.775 mm | 0.188 in

Height 1.70 mm | 0.07 in

Length 460.00 mm | 18.11 in

Width 7.00 mm | 0.28 in

Environmental Specifications

Operating Temperature -60 °C to +115 °C (-76 °F to +239 °F)

General Specifications

Hanger Type Cable tie

Accessories Adapters

Color Black

Material Type Heat-stabilized weather resistant nylon

Ordering Note CommScope® standard product in the United States and Canada

Package Quantity 100

Mechanical Specifications

Mounting Angle member | Cable ladder | Round member

Tensile Force 533.8 N | 120.0 lbf

Packed Dimensions

Shipping Weight 0.54 kg | 1.19 lb

Regulatory Compliance/Certifications

Agency	Classification
CSA	
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

