

CB-LH-25

Locking Heads for Cable Banding CB-12-50, 25 pcs (uses CB-IT installation tool - not incl)



Product Classification

Product Type Banding

Dimensions

Height 12.57 mm | 0.49 in

Length 21.59 mm | 0.85 in

Width 19.05 mm | 0.75 in

Environmental Specifications

Operating Temperature -65 °C to +90 °C (-85 °F to +194 °F)

General Specifications

Adapter Type Adapter

Color Black

Material Type Heat-stabilized weather resistant acetal

Ordering Note CommScope® standard product in the United States and Canada

Package Quantity 25

Mechanical Specifications

Mounting Round member

Regulatory Compliance/Certifications

Agency **Classification**

CSA

RoHS 2011/65/EU

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

