



Lace-up Hoisting Grip for 1-5/8 in coaxial cable and elliptical waveguide 44, 52, and 63

## Product Classification

**Product Type** Hoisting grip

## Dimensions

**Nominal Size** 1-5/8 in  
**Grip Length, minimum** 685.80 mm | 27.00 in  
**Leader Length, minimum** 304.80 mm | 12.00 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## General Specifications

**Hoisting Grip Type** Lace-up hoisting grip  
**Attachment Spacing Intervals** 61 m | 200 ft  
**Material Type** Stainless steel  
**Ordering Note** CommScope® standard product in the United States and Canada  
**Package Quantity** 1  
**Support Clamp** Not included  
**Tool Type** Hoisting grip

## Mechanical Specifications

**Pull Load Capacity** 950 lb

## Packed Dimensions

**Height** 3.8 cm | 1.5 in  
**Length** 24.0 cm | 9.4 in  
**Width** 22.4 cm | 8.8 in  
**Shipping Weight** 0.40 kg | 0.88 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)

