



Lace-up Hoisting Grip for 7/8 in corrugated, smoothwall, and braided coaxial cable

OBSOLETE

This product was discontinued on: November 4, 2015

Product Classification

Brand	I-Line
Product Type	Hoisting grip

Dimensions

Nominal Size	7/8 in
Grip Length, minimum	431.80 mm 17.00 in
Leader Length, minimum	330.20 mm 13.00 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hoisting Grip Type	Lace-up hoisting grip
Attachment Spacing Intervals	61 m 200 ft
Material Type	Tin-coated bronze
Ordering Note	CommScope® non-standard product
Package Quantity	1
Support Clamp	Not included
Tool Type	Hoisting grip

Mechanical Specifications

Pull Load Capacity	500 lb
---------------------------	--------

Packed Dimensions

Height	17.0 cm 6.7 in
Length	27.0 cm 10.6 in
Width	8.0 cm 3.1 in
Shipping Weight	0.33 kg 0.72 lb