

L4SGRIP



Support Hoisting Grip for 1/2 in coaxial cable

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 1/2 in
Grip Length, minimum 254.00 mm | 10.00 in
Leader Length, minimum 177.80 mm | 7.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Support hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Installation Tool Required; not included
Material Type Stainless steel
Ordering Note CommScope® standard product (Global)
Package Quantity 1
Support Clamp Included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 500 lb

Packed Dimensions

Height 17.0 cm | 6.7 in
Length 28.0 cm | 11.0 in

L4SGRIP

Width 8.0 cm | 3.1 in
Shipping Weight 0.30 kg | 0.66 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

