



Trunk fitting kit with 12 cable glands

Product Classification

Product Type Gland kit
Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Construction Materials

Material Type EPMM Rubber | Nylon 66

Dimensions

Height 56.00 mm | 2.20 in
Width 40.00 mm | 1.57 in

Environmental Specifications

Environmental Space Indoor
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity Up to 95%, non-condensing
Safety Standard CE
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Application Used in conjunction with HD,UD and EHD Panels
Color Black
Package Quantity 12
Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

