



NOKIA® CPRI Digital Donor CPRI-N V7.0 supported

- Supports up to 24 AxCs per card in FDD mode
- Supports up to 4 AxCs per card in TDD mode
- Supports Line Rates 3, 5 and 7 and auto-negotiation of the line rate in FDD mode
- Supports Line Rate 7 in TDD mode

Product Classification

Product Type	Card
Product Brand	ERA®

General Specifications

Device Type	Card
General Alarm	Integrated into management system
Input Connector Interface	SFP+
Input Connector, quantity	6
Management Interface	Integrated into management system
Note	Detailed Product Specifications are available. Please contact your local ANDREW representative.
Required Subrack Version	WCS-2 SUBRACK (7635443-03) WCS-2 SUBRACK (A7635443-03) WCS-4 SUBRACK (7635442-03) WCS-4 SUBRACK (A7635442-03) WCS2 SUBRACK, INTEGRATED DC PSU (7844067-02) WCS2 SUBRACK, INTEGRATED DC PSU (A7844067-02) WCS4 SUBRACK, INTEGRATED DC PSU (7844068-02) WCS4 SUBRACK, INTEGRATED DC PSU (A7844068-02)

Dimensions

Height	20 mm 0.787 in
Width	145 mm 5.709 in
Depth	300 mm 11.811 in

Packaging and Weights

Weight, net	0.47 kg 1.036 lb
--------------------	--------------------