

# RG142-NMNM-1M5

---

RG142 Braided Jumper with interface types N Male and N Male, 1.5m



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Series</b>	RG142

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	RG142
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	1.5 m   4.921 ft
---------------	------------------

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.152	23

## Jumper Assembly Sample Label

# RG142-NMNM-1M5

---



## Included Products

- RG142 – RG142 50 Ohm Braided Coaxial Cable
- RG142TNM-CR – Type N Male for RG142 braided cable