

# 760248830 | BUDI-FM-TL148-US00



BUDI™ Fiber Optic Wall Mount Enclosure for Splice/Patch, 48 LC/UPC adapters

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Wall box
<b>Product Brand</b>	BUDI™
<b>Product Series</b>	BUDI-FM
<b>Country Specific for</b>	United States
<b>Warranty</b>	For more information, please consult our Product Warranty guidelines

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Adapter Ports, quantity</b>	48
<b>Adapters, quantity</b>	48
<b>Color</b>	Gray
<b>Interface</b>	LC/UPC
<b>Mounting</b>	Wall mount
<b>Patching Capacity, maximum</b>	48
<b>Pigtails Included, quantity</b>	48

## Dimensions

<b>Height</b>	480 mm   18.898 in
<b>Height, with cover</b>	550 mm   21.654 in
<b>Width</b>	360 mm   14.173 in
<b>Depth</b>	175 mm   6.89 in

## Material Specifications

<b>Material Type</b>	PC/ABS
----------------------	--------

## Environmental Specifications

<b>Environmental Space</b>	Indoor/Outdoor
<b>Flammability Rating</b>	UL 94 V-0
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines