

# 1P2132-000 | FIBRBOX-B-12-1-AS

---

FIBRBOX Fiber Optic pedestal, wall, or pole mount splice enclosure, Buffer tube storage up to 96 fiber cable, 120 single splices or 288 mass fusion, with ground block, and gasket sealed door

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Single-ended, rectangular fiber closure

## General Specifications

<b>Functionality</b>	Splicing
<b>Access</b>	Front
<b>Cable Entry Location</b>	Bottom
<b>Enclosure Color</b>	Almond
<b>Front Cover Type</b>	Hinged with lock
<b>Mounting</b>	Pedestal   Pole   Wall
<b>Port, quantity</b>	24
<b>Splice Tray Construction</b>	SC (Single circuit)
<b>Splice Trays</b>	Included
<b>Splice Trays Included, quantity</b>	1
<b>Splicing Capacity, maximum</b>	12
<b>Splicing Type</b>	Heat shrink, mass fusion   Heat shrink, single fiber fusion
<b>Splicing Type, Supported</b>	Mass fusion   Single fusion

## Dimensions

<b>Height</b>	462.84 mm   18.222 in
<b>Width</b>	152.4 mm   6 in
<b>Depth</b>	106.68 mm   4.2 in

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

# 1P2132-000 | FIBRBOX-B-12-1-AS

---

## Environmental Specifications

<b>Environmental Space</b>	Indoor/Outdoor
<b>Qualification Standards</b>	IEC 60529, IP54   IEC 61753-1, category G

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton