

# 760258661 | FMS-K1BI-S5M4-24-SP-EU



FMS Fiber Optic Panel, 1U, 19 in, black, Includes 12 x SC OM4 Duplex Adaptors (24F), 24 x MM SC Pigtails. 24 x Splice protectors. Splice tray and cable glands

## Product Classification

|                              |                          |
|------------------------------|--------------------------|
| <b>Regional Availability</b> | EMEA                     |
| <b>Portfolio</b>             | CommScope®               |
| <b>Product Type</b>          | Fiber patch/splice panel |
| <b>Product Series</b>        | FMS                      |

## General Specifications

|  |                                  |
|--|----------------------------------|
| <b>Functionality</b>                   | Patching   Splicing              |
| <b>Body Style</b>                      | Symmetrical                      |
| <b>Cable Exit Location</b>             | Rear, left side                  |
| <b>Color</b>                           | Black                            |
| <b>Interface, front</b>                | SC/UPC                           |
| <b>Fiber Color Code</b>                | TIA-598                          |
| <b>Rack Type</b>                       | EIA 19 in                        |
| <b>Rack Units</b>                      | 1                                |
| <b>Shelf Movement</b>                  | Sliding                          |
| <b>Splice Trays Included, quantity</b> | 1                                |
| <b>Splicing Type</b>                   | Heat shrink, single fiber fusion |
| <b>Total Ports, quantity</b>           | 24                               |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 44.3 mm   1.744 in   |
| <b>Width</b>  | 482.2 mm   18.984 in |
| <b>Depth</b>  | 344.2 mm   13.551 in |

## Material Specifications

|               |               |
|---------------|---------------|
| <b>Finish</b> | Powder coated |
|---------------|---------------|

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM4

**Insertion Loss, maximum** 0.3 dB

**Return Loss, minimum** 27 dB

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| Agency     | Classification   |
|------------|--|
| CHINA-ROHS | Above maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant/Exempted   |
| UK-ROHS    | Compliant/Exempted   |

