

760258038 | HCA-ACC-3mm SC/APC Test Lead 40FT, 3x Cvtr



HCA-ACC-3mm SC/APC Test Lead 40FT, Full size, DLX and Bayonet converter included

- Prodigy converters simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability	North America
Product Type	Fiber test patch cord
Product Brand	PRODIGY™
Product Series	HCA

General Specifications

Color, boot A	Black
Color, connector A	Black
Color, connector B	Green
Interface, Connector A	Prodigy
Interface, Connector B	SC/APC
Jacket Color	Yellow

Dimensions

Cable Assembly Length	12.192 m 40 ft
------------------------------	------------------

Mechanical Specifications

Dust Cap Pulling Force, minimum	445 N 100.04 lbf
--	--------------------

Optical Specifications

Insertion Loss, maximum	0.3 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

760258038 | HCA-ACC-3mm SC/APC Test Lead 40FT, 3x Cvtr

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Indoor/Outdoor
Qualification Standards	IEC 60793 IEC 60794