

# XP-RM1U-4C



XPND 1Ru empty panel, accepts 4 XPND modular cassettes, providing up to 48 SC ports or 96 LC ports

- Components can be installed and removed from front or rear of panel
- Supports 8f, 12f, 16f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be securely attached in the rear of panel

## Product Classification

Regional Availability	Latin America   North America
Product Type	Fiber patch panel
Product Brand	XPND®

## General Specifications

Color	White
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	0

## Dimensions

Height	133.5 mm   5.256 in
Width	431.8 mm   17 in
Depth	304.8 mm   12 in

## Material Specifications

Material Type	Aluminum   Steel
---------------	------------------

## Environmental Specifications

Safety Standard	c-UL-us
-----------------	---------

## Packaging and Weights

Packaging quantity	1
--------------------	---

# XP-RM1U-4C

**Weight, net** 5.375 kg | 11.85 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

